

# THE ALPHABOND REVIEW

REVOLUTIONARY PRODUCTS FOR YOUR DENTAL NEEDS

www.alphabond.com.au

ISSUE 02

2015



## GLAZE - SELF CURE ACRYLIC RESIN

Glaze™ is a fast-setting, crystal clear self-curing acrylic resin which bonds to other resin substrates and dries to a clear, hard surface with a high-gloss finish. Glaze™ can be brushed onto a clean composite or acrylic material in or out of the mouth to achieve a polished surface that enhances the appliance and reduces the need for additional polishing. Recommended for use on provisional, relines, and orthodontic appliances, Glaze™ fills microscopic voids and reduces bacterial growth and odour. Sets in 10-20 seconds.



(Order code: KEY0921236)

**NEW**

## INDENCO Triumph Investment & Liquid

One Investment for all dental necessities! An investment of choice for pressable ceramics including Zirconium & Lithium Disilicate.

Offering extended working time, easy pouring, and ensures extremely smooth casting and pressed ceramic surfaces.

Compatible with all types of burnout and casting techniques; Traditional Rings, Ring-less, Traditional burnout (slow), or Rapid burnout techniques (fast).

(Order code: IND-INTRC60)



## HIGH LUSTRE BUFF



Bredent's High Luster Buff Acrylic. Made from natural linen, these buffs are ready for immediate use on a polishing motor and can be used easily and without fraying. Specially selected fabrics prevent the acrylic from overheating.

Order code: 100mm - 35 layers - BR35000820



## WAX SPRUES

Thanks to their design, the special casting channels improve the casting result.

With Bredent's 3.5mm sprue you can create the ideal prerequisite for each casting system

(Order code: BR43001445)

## TEMPOGEL

LANG's very soft relines for Temporary cushion treatment treats & soothes sensitive gingival and ridge areas. (100g/118ml)  
(Order code: HARRTEMP)



## TWIST by EVE

EVE's DiaComp Plus Twist set gives you Medium pre-polishing and Fine high-shine polishing all in one.  
(Order code: EVE-HP125)



**ALPHABOND** dental

www.alphabond.com.au Ph: (02) 9417 6660 E-mail: info@alphabond.com.au



Like us on Facebook



## CENTRI-FUSE DECALS

Keystone's Centri-Fuse kit will allow you to apply decals to mouthguards quicker, easier and cost effectively. Using a Flameless torch, create superb clarity and adhesion while eliminating bubbles. In the kit, you get 20 centri-fuse strips, a flameless torch, a primer, one brush, a pair of scissor, one trimming and polishing brush and pre-printed decals.

(Order code: KEY10091000)

## APPLIANCE CARE

Offer your clients a new alternative for cleaning and storing their dental appliance with the PROZCARE kit. Using an organically certified non-abrasive paste made from peppermint, together with a special designed brush will leave any fixed or removable dental appliances with a clean fresh taste with a shiny gloss finish.


Prozcare also offers you the ability to order replacements in the paste, brush and box, should your client ever need more.

(Order code: \_\_\_\_)



## GIFLEX-TR by BREDENT

With Bredent's Giflex-TR, it's possible to separate the arch from the basal direction if preparation margins are close to each other. The segmented design of the Giflex-TR allows rapid removal of grinding dust so that jamming of the disc is avoided.



(Order code: BR34000120)

## LAY-ART BRUSHES by RENFERT

Designed for efficiency and reliability, using the best hair. The result is an extremely stable brush tip, which becomes more pointed rather than blunt, thus reducing the build-up of porcelain particles

(Order code: R1725-1000)




### FIBER FORCE

Fabricate your frameworks with SYNCA's fatigue resistant Fiber Force mesh. A light-curing pre-impregnated fiber reinforcement system perfectly matching the PRECI Perma-Ret System. Pink mesh 53mm x 80 mm.

(Order code SYN08004)

## DYNEX DISCS



Renfert's Dynex separating discs are highly precise tools. They have a cutting speed of up to 300 km/h allowing them to separate powerfully, safely and precisely. Extremely thin and flexible diamond abrasive and separating disc with glass fiber reinforcement. Created for separating and trimming porcelain, zircon oxide and lithium disilicate.

(Order code SYN08004)

## POLISHING SET FOR DENTURES

EVE's Denture Polishing Set of 7, will allow you to shape, smooth, pre-polish, polish and finish with a high-shine polish in one complete set.



(Order code: BR34000120)



# ALPHABOND dental

www.alphabond.com.au Ph: (02) 9417 6660 E-mail: info@alphabond.com.au



Like us on Facebook